

CT-3 DIP Switch configuration guide  
-----

DIP Switch Setting:

-MM cartridge : DIP 7 ON, else OFF, input impednace 4.7K Ohm

-MC Cartridge (Ohm):

input impedance 2.7K : 6 ON, else OFF

input impedance 1.35K : 2,6 ON, else OFF

input impedance 900 : 3,6 ON, else OFF

input impedance 430 : 4,6 ON, else OFF

input impedance 230 : 5,6 ON, else OFF

input impedance 150 : 2,3,4,5,6 ON, else OFF

No impedance match your need?

-want to use match the impedance for yourself, DIP 6ON, else off, and switch the DIP 1 resistor with the value you want.